


未注公差/General tolerances(mm)															2	3	4	5	6
0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500	REV	ECN	DESCRIPTION	DRFT	DATE	
~	~	~	~	~	~	~	~	~	~	~	~	~	~	0.1/10					
3	6	10	18	30	50	80	120	180	250	315	400	500	>500						



A

A





B

B



C

C



PCB Layout

DBT40C — 13.0 — XXP — C — S/P

(Series No.) (Pitch) (Poles)

Slotted/Phillips

(Color):GN:(Green), BK:(Black), BU:(Blue), RD:(Red), GY:(Gray)
OG:(Orange), WT:(White), YL:(Yellow), CR:(Clear)

UL 标准/UL Standard:	
额定电压/电流/Rated Voltage(V)/Current(A)	600/40
IEC 标准/IEC Standard:	
额定电压/电流/Rated Voltage(V)/Current(A)	1000/41
耐压 Withstanding Voltage (kV/Min)	3.0
螺丝扭矩/Torque Tightening(N·m/Lb.in)	1.2/10.53
线径范围(硬线和软线)/Wire Range(rigid and flexible)(mm²/AWG)	6.0/18~10
间距/Pitch(mm)/线数范围/Poles	13.0/02~24
使用温度范围/Operating temperature(°C)	-40~+105
符合RoHS环保要求/Conform to RoHS	Yes

3

4

5

6

4

5

6

MAT NO.:	/	DORABO 宁波地博电气有限公司	
STATUS:	/	NINGBO DORABO ELECTRICAL CO., LTD	
APPD:	JTing Chen 2025.10.22	NAME: DBT40C-13.0-XXP-C-P	
CHKD:	Duck Mao 2025.10.22	DRAWING NO.: /	
DRFT:	Steven Lu 2025.10.22	REV	M1
SIZE:A4	mm (inch)	TYPE: CUSTOMER_DRAWING	SCALE: 1:1
		SHEET	1/1

1

2

3

4

5

6