

标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE

A

B

C

D

E

F

G

A

B


C

D



E

F


G



1. 额定电压/电流: 300V/16A
2. 额定脉冲电压: 4kv
3. 线径范围(硬线&软线)  
(mm<sup>2</sup>/AWG): 0.5...2.5/20...12
4. 间距/线数范围: 5.0/N=2~12P
5. 剥线长度: 10-12mm
6. 使用温度范围: -40℃~+85℃



|    |    |      |       |    |
|----|----|------|-------|----|
| 2  | 接触 | 铜    | 镀镍锡   |    |
| 1  | 基座 | PA66 | 灰色    |    |
| 序号 | 品名 | 材质   | 电镀/颜色 | 备注 |

|                                                                                       |             |               |               |                                                                                       |
|---------------------------------------------------------------------------------------|-------------|---------------|---------------|---------------------------------------------------------------------------------------|
|  | 深圳市虹成电子有限公司 |               | 品名<br>TITLE   | 接线端子                                                                                  |
|                                                                                       |             |               | 料号<br>PART NO | HC-JXDZRP-5.0-4P                                                                      |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                                              |             | 比列<br>SCALE   | 1:1           |  |
| 0~3                                                                                   | ±0.12       | 3~6           | ±0.18         |  |
| >6~10                                                                                 | ±0.22       | >10~18        | ±0.26         |                                                                                       |
| >18~30                                                                                | ±0.31       | >30~50        | ±0.37         | 审核<br>CHECKED                                                                         |
| >50~80                                                                                | ±0.57       | >120~180      | ±0.80         |                                                                                       |
| >180~250                                                                              | ±0.93       | >250~315      | ±1.05         | 批准<br>APPROVE                                                                         |
| >315~400                                                                              | ±1.60       | >400~500      | ±2.20         |                                                                                       |
| >500                                                                                  | ±2.50       |               |               |                                                                                       |
| 单位<br>UNIT                                                                            | MM          | 制图<br>DRAW    | AhYe          |                                                                                       |
| 张数<br>PART NO                                                                         | 1 OF 1      | 审核<br>CHECKED | 夏操云           |                                                                                       |
| 版本<br>REV                                                                             | A           | 批准<br>APPROVE | 赵亮亮           |                                                                                       |