







标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

3D VIEW

PIN 数	A±0.2	B±0.2	C±0.2
2P	6.00	3.60	1.50
3P	7.50	5.10	3.00
4P	9.00	6.60	4.50
5P	10.50	8.10	6.00
6P	12.00	9.60	7.50

RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.1)

Specifications:

1. Rated Voltage : 100V AC/DC
2. Rated Current : 1A AC,DC
3. Withstand Voltage : 500V AC/minute
4. Contact Resistance : 50mΩ(MAX.)
5. Insulation Resistance : 500MΩ(MIN.)
6. Storage Temperature Range : -40°C~+85°C;
7. Operation Temperature Range : -25°C~+70°C;

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HC-ZH1. 5-2PWT

UNLESS OTHERWISE,
GENERAL TOLERANCE:比 例
SCALE

1:1

X. xxx ±0.10
X. xx ±0.20
X. x ±0.30单 位
UNIT

MM

ANGULAR:
X. xx° ±1°
X. x° ±3°
X. ° ±5°张 数
PART NO

1 OF 1

制 图
DRAW
审核
CHECKED
批准
APPROVEAhYe
夏操云
赵亮亮