

### 电气特性/Electrical Specification





额定参数/Rated	250V 10A
接触电阻/Contact Resistance	20mΩ MAX
绝缘电阻/Insulation Resistance	5000mΩ/1000V
抗电强度/Dielectric Strength	2000V/1 min

### 机械特性/Mechanical Specification

使用温度/Temp range	-40° C ~ +105° C
瞬间温度/MAX Soldering	+250° C/5s

### 部件材质/Part&Material

塑件/Housing	PA66 UL94 V-0
端子/Terminal	黄铜 镀锡/Brass Tin plating



间距公差/Spacing tolerance(mm) — □ ▽

X.	X.X	X.X.X	0.1/10	
±0.5	±0.30	±0.1	∠±2°	

未注公差/General tolerances(mm)

0---30	31---50	51---80	81---120	>121
±0.30	±0.50	±0.70	±1.05	±1.20




连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

STATUS APPD CHKD DRFT DATE CUSTOM PROJECT UNITS

ZH



MM

PART NAME:

PART NO: LXW5.08EGR-NP

DRAWING NO:

TYPE: CUSTOMER DRAWINGS

REV SIZE SHEET

A A4 1/1