




Specifications:
Rated Voltage : 125V AC/DC
Rated Current : 1A AC,DC
Withstand Voltage : 200V AC/minute
Contact Resistance : 50mΩ(MAX.)
Insulation Resistance : 100MΩ(MIN.)
Storage Temperature Range: -40°C~+85°C;
Operation Temperature Range: -25°C~+70°C;

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注
	品名 TITLE	针座		
	料号 PART NO	HC-MX1.25-6PLT		
UNLESS OTHERWISE, GENERAL TOLERANCE:		比列 SCALE	1:1	制图 DRAW
X. xxx ±0.05 X. xx ±0.15 X. x ±0.25		单位 UNIT	MM	审核 CHECKED
ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°		张数 PART NO	1 OF 1	夏操云
		版本 REV	A	批准 APPROVE
				赵亮亮

PIN 数	A±0.1	B±0.1	C±0.1
2P	7.60	4.50	1.25
3P	8.85	5.75	2.50
4P	10.10	7.00	3.75
5P	11.35	8.25	5.00
6P	12.60	9.50	6.25



深圳市虹成电子有限公司

