



标记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修改 REVISE	日期 DATE	核准 APPROVE



材料及电镀




1. 塑件主体: PA66,
2. 焊 针: 黄铜, 镀镍

电气性能

- 额定电压: 300V
- 额定电流: 15A
- 接触电阻: 20mΩ (Max)
- 绝缘电阻: 500MΩ \ DC500V
- 耐 电 压: AC2000V \ 1Min

机械性能

- 温度范围: -40℃ ~ +105℃
- 瞬时温度: +250℃ , 5秒



2	方盒	铜	镀镍	
1	基座	PA66	绿色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司 品名 TITLE 料号 PART NO		接线端子 HC-JXDZR-5.08-9P											
	GENERAL TOLERANCES (UNLESS SPECIFIED)	比列 SCALE 1:1												
<table border="1"> <tr> <th>公差参数</th> <th>未注明公差:</th> </tr> <tr> <td>2-6P ±0.10 ±0.20</td> <td>X.xxx ±0.10</td> </tr> <tr> <td>7-12P ±0.20 ±0.30</td> <td>X.xx ±0.20</td> </tr> <tr> <td>13-16P ±0.25 ±0.40</td> <td>X.x ±0.30</td> </tr> <tr> <td>18-24P ±0.30 ±0.50</td> <td></td> </tr> </table>	公差参数	未注明公差:	2-6P ±0.10 ±0.20	X.xxx ±0.10	7-12P ±0.20 ±0.30	X.xx ±0.20	13-16P ±0.25 ±0.40	X.x ±0.30	18-24P ±0.30 ±0.50		单位 UNIT MM	张数 PART NO 1 OF 1	制图 DRAW AhYe	审核 CHECKED 夏操云
公差参数	未注明公差:													
2-6P ±0.10 ±0.20	X.xxx ±0.10													
7-12P ±0.20 ±0.30	X.xx ±0.20													
13-16P ±0.25 ±0.40	X.x ±0.30													
18-24P ±0.30 ±0.50														
	版本 REV A		批准 APPROVE 赵明亮											