






标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN 数	A±0.15	B±0.15	C±0.15	D±0.15
2P	4.30	1.00	3.25	2.65
3P	5.30	2.00	4.25	3.65
4P	6.30	3.00	5.25	4.65
5P	7.30	4.00	6.25	5.65
6P	8.30	5.00	7.25	6.65
7P	9.30	6.00	8.25	7.65
8P	10.30	7.00	9.25	8.65





3D View



Specifications:

- 1.Rated Voltage : 50V AC/DC
- 2.Rated Current : 1A AC,DC
- 3.Withstand Voltage : 200V AC/minute
- 4.Contact Resistance : 50mΩ(MAX.)
- 5.Insulation Resistance : 100MΩ(MIN.)
- 6.Storage Temperature Range: -40°C~+85°C;
- 7.Operation Temperature Range: -25°C~+70°C;



2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HC-SH1.0-8PLT

GENERAL TOLERANCES
(UNLESS SPECIFIED)X. xxx ±0.05
X. xx ±0.15
X. x ±0.25

ANGULAR:

X. xx° ±1°
X. x° ±3°
X. ° ±5°比 例
SCALE

1:1

单 位
UNIT

MM

张 数
PART NO

1 OF 1

版 本
REV

A

制 图
DRAW

AhYe

审 核
CHECKED

夏操云

批 准
APPROVE

赵亮亮

