







标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN	DIM A	DIM B	DIM C
2P	8.00	4.80	2.00
3P	10.00	6.80	4.00
4P	12.00	8.80	6.00
5P	14.00	10.80	8.00
6P	16.00	12.80	10.00
7P	18.00	14.80	12.00
8P	20.00	16.80	14.00



RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.1)

Specifications:

1. Rated Voltage: 125V AC/DC
2. Rated Current: 2A AC, DC
3. Withstand Voltage: 200V AC/minute
4. Contact Resistance : 50mΩ (Max)
5. Insulation Resistance: 1000MΩ (MIN)
6. Storage Temperature e Range: -40℃ ~ +85℃;
7. Operation Temperature Range: -25℃ ~ +70℃;

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品 名		针座		
			TITLE				
			料 号		HC-PH2. 0-4PLT		
			PART NO				
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 列	1 : 1			
X. xxx ±0. 10			单 位	MM	制 图		
X. xx ±0. 20			UNIT		DRAW		AhYe
X. x ±0. 30			张 数	1 OF 1	审 核		夏操云
			PART NO		CHECKED		
X. xx° ±1°			版 本	A	批 准		赵亮亮
X. x° ±3°			REV		APPROVE		
X. ° ±5°							