








NOTES:
1.ELECTRICAL CHARACTERS:
1-1.RATING: DC 125V 1.5A;
1-2.CONTACT RESISTANCE: $\leq 40m\Omega$;
1-3.INSULATION RESISTANCE: $\geq 500M\Omega$;
1-4.WITHSTANDING VOLTAGE: AC 500V 1min;
1-5.LIFE: 750 CYCLES;



PCB HOLES(TOP VIEW)
GENERAL TOLERANCE: $\pm 0.05mm$

③	PIN	8	Phosphor copper $t=0.3$	Au Sn PLATED	
②	SHELL	2	BRASS $T=0.2$	Ni PLATED	
①	HOUSING	1	LCP	BLACK	
No.	PART NAME	Q'ty	MATERIAL	REMARK	

TOLERANCE UNLESS OTHERWISE SPEC			SHENZHEN FUGANG TECHNOLOGY CO.,LTD			
BASIC DIMENSION	TOLERANCE	DSND	W	F	TITLE: RJ45 JACK	
x.x	± 0.50	CHKD	L	P U	PART NO: RJ-068T-1-6	
x.xx	± 0.30	APVD	L	Z W		
x.xxx	± 0.10					
ANGLES	$\pm 3^{\circ}$					



UNIT:mm

SCALE:1:1

SIZE:A4

SHEET:1/1