






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE
PIN数	A±0.15	B±0.15	C±0.15	D±0.15
2P	4.30	1.00	3.25	2.65
3P	5.30	2.00	4.25	3.65
4P	6.30	3.00	5.25	4.65
5P	7.30	4.00	6.25	5.65
6P	8.30	5.00	7.25	6.65
7P	9.30	6.00	8.25	7.65
8P	10.30	7.00	9.25	8.65





3D View



Specifications:

- 1.Rated Voltage : 50V AC/DC
- 2.Rated Current : 1A AC,DC
- 3.Withstand Voltage : 200V AC/minute
- 4.Contact Resistance : 50mΩ(MAX.)
- 5.Insulation Resistance : 100MΩ(MIN.)
- 6.Storage Temperature Range: -40℃~+85℃;
- 7.Operation Temperature Range: -25℃~+70℃;

RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.1)

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE		针座		
料号 PART NO		HC-SH1.0-7PWT		
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	
X. xxx ±0.05 X. xx ±0.15 X. x ±0.25		单 位 UNIT	MM	制 图 DRAW
ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°		张 数 PART NO	1 OF 1	审 核 CHECKED
		版 本 REV	A	批 准 APPROVE
				夏操云 赵亮亮

