








标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN	DIM A	DIM B	DIM C
2P	10.00	6.10	2.50
3P	12.50	8.60	5.00
4P	15.00	11.10	7.50
5P	17.50	13.60	10.00
6P	20.00	16.10	12.50
7P	22.50	18.60	15.00
8P	25.00	21.10	17.50

RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE ± 0.1)

SPECIFICATION

1. Contact resistance: $\leq 10\text{M}\Omega$
2. Insulation resistance: $\geq 1000\text{M}\Omega$
3. Rated voltage: 250 V AC DC
4. Rated current: 3.0 A AC DC
5. Withstand Voltage: 1000V AC/minute
6. Temperature Range : $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品名 TITLE	针座
			料号 PART NO	HC-XH2. 54-5PWT
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1	
X. xxx ± 0.10 X. xx ± 0.20 X. x ± 0.30 X. xx° ± 1° X. x° ± 3° X. ° ± 5°		单位 UNIT	MM	
		张数 PART NO	1 OF 1	审核 CHECKED
		版本 REV	A	批准 APPROVE
		制图 DRAW		夏操云
		批 准		赵亮亮

