











PCB参考图



视图 A-A

- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -25° C~85° C.
 3. 额定电压: 250V, AC
 4. 接触电阻: ≤30mΩ
 5. 绝缘电阻: ≥100mΩ

NP	A	B	C	D	E
2	7.45	/	1.25	3.00	/
3	8.70	/	2.50	4.25	2.00
4	9.95	4.60	3.75	3.00	3.00
5	11.20	5.90	5.00	4.05	2.25
6	12.45	7.10	6.25	5.30	3.50
7	13.70	6.25	7.50	4.05	
8	14.95	7.50	8.75	5.30	
9	16.20	7.85	10.00	6.55	
10	17.45	10.00	11.25	7.80	4.75
11	18.70	11.25	12.50	9.05	
12	19.95	12.50	13.75	10.30	
13	21.20	13.75	15.00	11.55	5.50
14	22.45	15.00	16.25	12.80	
15	23.70	16.25	17.50	14.05	8.00
16	24.95	17.50	18.75	15.30	

序号	名称	材质	电镀	备注
4	吸盖	LCP 黑色	—	
3	焊片	黄铜 T=0.3	锡	
2	端子	磷铜 T=0.3	锡	
1	底座	LCP 黑色	—	

浙江富港电子有限公司
ZhejiangFugang Electronics Co.,Ltd

产品名称: 1.25CB-LT-NP
产品编号:

未注公差按以下要求			制图	吴雨蓓	2025-12-27	图号: WI-E-001-1667	本: A0	单位: mm	比例: 1:1	视图: 	
DIM	TOL	DIM	DEC	审核	向宇宙						2025-12-27
X	±0.20	X°	±5.00°	批准	黄文丹						2025-12-27
X, X	±0.10	X, X°	±3.00°								
X, XX	±0.05	X, XX°	±2.00°								
X, XXX	±0.02	X, XXX°									

版本	变更标记	变更内容	日期	修订	审核	批准
A0		新版发行	2025-12-27			