






RoHS



NOTES:

1. MATERIAL:

HOUSING: LCP (UL94-V0), COLOR: NATURAL.
COVER: LCP OR PA (UL94-V0), COLOR: BLACK.
CONTACT: COPPER ALLOY;
LEG: COPPER ALLOY;

2. PLATING:

CONTACT: GOLD OR TIN PLATED ON NICKEL OVERALL.
LEG: TIN PLATED ON NICKEL OVERALL.

RATING:

CURRENT RATING: 0.4A AC/DC
VOLTAGE RATING: 50V AC/DC
TEMPERATURE RANGE: -55°C~+85°C;


PIN NO.	DIM. A	DIM. B	DIM. C	DIM. D
4	3.80	1.50	2.60	3.30
5	4.30	2.00	3.10	3.80
6	4.80	2.50	3.60	4.30
7	5.30	3.00	4.10	4.80
8	5.80	3.50	4.60	5.30
9	6.30	4.00	5.10	5.80
10	6.80	4.50	5.60	6.30
12	7.80	5.50	6.60	7.30
13	8.30	5.00	6.10	7.80
14	8.80	6.50	7.60	8.30
15	9.80	7.00	8.10	8.80
16	9.80	7.50	8.60	9.30
18	10.80	8.50	9.60	10.30
20	11.80	9.50	10.60	11.30
22	12.80	10.50	11.60	12.30
24	13.80	11.50	12.60	13.30
26	14.80	12.50	13.60	14.30
28	15.80	13.50	14.60	15.30
30	16.80	14.50	15.60	16.30
40	21.80	19.50	20.60	21.30
n	n*0.5+1.80	(n-1)*0.5	n*0.5+0.6	n*0.5+1.30

TOLERANCE UNLESS
OTHERWISE SPEC

SHENZHEN FUGANG TECHNOLOGY CO.,LTD


BASIC DIMENSION	TOLERANCE	DSND	S	L	26.01.20	TITLE: FPC SOCKET
x.x	±0.30	CHKD	L	P	J	26.01.20
x.xx	±0.20	APVD	L	Z	W	26.01.20
x.xxx	±0.10					
ANGLES	±3°					
					UNIT: mm	SCALE: 1:1
					SIZE: A4	SHEET: 1/1

RoHS



NOTE:

- 1.10 Sprocket hole pitch cumulative tolerance ± 0.20 .
2. Carrier camber is within 1mm in 100mm.
3. Material: black conductive polystyrene alloy.
4. Material Thickness: 0.3 ± 0.05 mm.
5. All dimensions meet EIA-481-B requirements.
6. 5000pcs Per Reel.
7. For tape width (dim W) 16 and 24mm pilot holes are provided on one sides.
For tape width (dim W) 32, 44 and 56mm pilot holes are provided on both sides.



PIN NO.	W	C	PCS /REEL	REEL/CARTON	SUM(PCS)
04PIN~12PIN	16	—	5000	13	65000
14PIN~30PIN	24	—	5000	10	50000
31Pin~40PIN	32	28.4	5000	7	35000
50PIN	44	38.4	5000	5	25000

TOLERANCE UNLESS OTHERWISE SPEC		SHENZHEN FUGANG TECHNOLOGY CO.,LTD					
BASIC DIMENSION	TOLERANCE	DSND	S	L	26.01.20	TITLE: FPC SOCKET	
x.x	±0.30	CHKD	L	P	J	26.01.20	PART NO: FG-FPC0510-NRL-TAG
x.xx	±0.20	APVD	L	Z	W	26.01.20	
x.xxx	±0.10						
ANGLES	±3°			UNIT: mm	SCALE: 1:1	SIZE: A4	SHEET: 1/1