







标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN	DIM A	DIM B	DIM C
2P	8.00	4.80	2.00
3P	10.00	6.80	4.00
4P	12.00	8.80	6.00
5P	14.00	10.80	8.00
6P	16.00	12.80	10.00
7P	18.00	14.80	12.00
8P	20.00	16.80	14.00




RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE ±0.1)

Specifications:

1. Rated Voltage: 125V AC/DC
2. Rated Current: 2A AC, DC
3. Withstand Voltage: 200V AC/minute
4. Contact Resistance: 50mΩ (Max)
5. Insulation Resistance: 1000MΩ (MIN)
6. Storage Temperature Range: -40℃ ~ +85℃;
7. Operation Temperature Range: -25℃ ~ +70℃;

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品名 TITLE	针座	
			料号 PART NO	HC-PH2.0-2PWT	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1		
X. xxx ±0.05	单位 UNIT	MM	制图 DRAW	AhYe	
X. xx ±0.15	张数 PART NO	1 OF 1	审核 CHECKED	夏操云	
X. x ±0.25	版本 REV	A	批准 APPROVE	赵亮亮	
X. xx° ±1°					
X. x° ±3°					
X. ° ±5°					