






| 标 记<br>MARK | ECN编号/变更内容<br>ECN NO/DEFINITION | 修 改<br>REVISE | 日 期<br>DATE | 核 准<br>APPROVE |
|-------------|---------------------------------|---------------|-------------|----------------|
|             |                                 |               |             |                |
| PIN 数       | A±0.15                          | B±0.15        | C±0.15      | D±0.15         |
| 2P          | 4.30                            | 1.00          | 3.25        | 2.65           |
| 3P          | 5.30                            | 2.00          | 4.25        | 3.65           |
| 4P          | 6.30                            | 3.00          | 5.25        | 4.65           |
| 5P          | 7.30                            | 4.00          | 6.25        | 5.65           |
| 6P          | 8.30                            | 5.00          | 7.25        | 6.65           |
| 7P          | 9.30                            | 6.00          | 8.25        | 7.65           |
| 8P          | 10.30                           | 7.00          | 9.25        | 8.65           |





3D View



## Specifications:

1. Rated Voltage : 50V AC/DC
2. Rated Current : 1A AC,DC
3. Withstand Voltage : 200V AC/minute
4. Contact Resistance : 50mΩ(MAX.)
5. Insulation Resistance : 100MΩ(MIN.)
6. Storage Temperature Range: -40°C~+85°C;
7. Operation Temperature Range: -25°C~+70°C;

RECOMMENDER P.C.B.LAYOUT TOP VIEW  
(COMPONENT SIDE TOLERANCE±0.1)

|    |    |     |       |    |
|----|----|-----|-------|----|
| 2  | 插针 | 铜   | 镀镍锡   |    |
| 1  | 基座 | LCP | 米色    |    |
| 序号 | 品名 | 材质  | 电镀/颜色 | 备注 |

|                                                                                       |             |               |               |                                                                                       |      |
|---------------------------------------------------------------------------------------|-------------|---------------|---------------|---------------------------------------------------------------------------------------|------|
|  | 深圳市虹成电子有限公司 |               | 品名<br>TITLE   | 针座                                                                                    |      |
|                                                                                       |             |               | 料号<br>PART NO | HC-SH1.0-6PLT                                                                         |      |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                                              |             | 比列<br>SCALE   | 1:1           |  |      |
| X. xxx ±0.05<br>X. xx ±0.15<br>X. x ±0.25                                             |             | 单位<br>UNIT    | MM            | 制图<br>DRAW                                                                            | AhYe |
| ANGULAR:<br>X. xx° ±1°<br>X. x° ±3°<br>X. ° ±5°                                       |             | 张数<br>PART NO | 1 OF 1        | 审核<br>CHECKED                                                                         | 夏操云  |
|                                                                                       |             | 版本<br>REV     | A             | 批准<br>APPROVE                                                                         | 赵亮亮  |

