

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN	DIM A	DIM B	DIM C
2P	8.00	4.80	2.00
3P	10.00	6.80	4.00
4P	12.00	8.80	6.00
5P	14.00	10.80	8.00
6P	16.00	12.80	10.00
7P	18.00	14.80	12.00
8P	20.00	16.80	14.00

A

B

C

D

E

F

G

Specifications:

1. Rated Voltage: 125V AC/DC
2. Rated Current: 2A AC, DC
3. Withstand Voltage: 200V AC/minute
4. Contact Resistance : 50mΩ (Max)
5. Insulation Resistance: 1000MΩ (MIN)
6. Storage Temperature e Range: -40℃ ~ +85℃;
7. Operation Temperature Range: -25℃ ~ +70℃;

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-PH2. 0-6PLT

GENERAL TOLERANCES
(UNLESS SPECIFIED)X. xxx ±0.10
X. xx ±0.20
X. x ±0.30X. xx° ±1°
X. x° ±3°
X. ° ±5°比 列
SCALE

1:1

单 位
UNIT

MM

张 数
PART NO

1 OF 1

版 本
REV

A

制 图
DRAW

AhYe

审 核
CHECKED




夏操云

批 准
APPROVE

赵亮亮



G

RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE ±0.1)