


标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE







PIN 数	A ± 0.2	B ± 0.2	C ± 0.2
2P	6.00	3.60	1.50
3P	7.50	5.10	3.00
4P	9.00	6.60	4.50
5P	10.50	8.10	6.00
6P	12.00	9.60	7.50



3D VIEW

Specifications:

1. Rated Voltage : 100V AC/DC
2. Rated Current : 1A AC,DC
3. Withstand Voltage : 500V AC/minute
4. Contact Resistance : 50m Ω (MAX.)
5. Insulation Resistance : 500M Ω (MIN.)
6. Storage Temperature Range: -40°C~+85°C;
7. Operation Temperature Range: -25°C~+70°C;

RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE ± 0.1)

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HC-ZH1.5-3PWT

UNLESS OTHERWISE,
GENERAL TOLERANCE:X. xxx ± 0.10
X. xx ± 0.20
X. x ± 0.30 ANGULAR:
X. xx° $\pm 1^\circ$
X. x° $\pm 3^\circ$
X. ° $\pm 5^\circ$ 比 例
SCALE

1:1

单 位
UNIT

MM

张 数
PART NO

1 OF 1

版 本
REV制 图
DRAW
审 核
CHECKED
批 准
APPROVEAhYe
夏操云
赵亮亮