








标记
MARKECN编号/变更内容
ECN NO/DEFINITION修改
REVISE日期
DATE核准
APPROVE

PIN 数	A±0.1	B±0.1	C±0.1
2P	7.60	4.50	1.25
3P	8.85	5.75	2.50
4P	10.10	7.00	3.75
5P	11.35	8.25	5.00
6P	12.60	9.50	6.25



3D View



Specifications:

- 1.Rated Voltage : 125V AC/DC
- 2.Rated Current : 1A AC,DC
- 3.Withstand Voltage : 200V AC/minute
- 4.Contact Resistance : 50mΩ(MAX.)
- 5.Insulation Resistance : 100MΩ(MIN.)
- 6.Storage Temperature Range: -40℃~+85℃;
- 7.Operation Temperature Range: -25℃~+70℃;

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HC-MX1.25-4PWT

UNLESS OTHERWISE,
GENERAL TOLERANCE:比列
SCALE

1:1

X. xxx ±0.05
X. xx ±0.15
X. x ±0.25单位
UNIT

MM

ANGULAR:
X. x° ±1°
X. x' ±3°
X. x'' ±5°张数
PART NO

1 OF 1

版本
REV

A

制图
DRAW审核
CHECKED批准
APPROVE

AhYe

夏操云

赵亮亮

