





标记
MARKECN编号/变更内容
ECN NO/DEFINITION修改
REVISE日期
DATE核准
APPROVE

Pin	DIM A	DIM B	DIM C
2	4.50	1.50	3.60
3	6.00	3.00	5.10
4	7.50	4.50	6.60
5	9.00	6.00	8.10
6	10.50	7.50	9.60
7	12.00	9.00	11.10
8	13.50	10.50	12.60
9	15.00	12.00	14.10
10	16.50	13.50	15.60
11	18.00	15.00	17.10
12	19.50	16.50	18.60
13	21.00	18.00	20.10
14	22.50	19.50	21.60
15	24.00	21.00	23.10
16	25.50	22.50	24.60



技术要求:

适应基板厚度: 1.2mm~1.6mm

温度范围: -25℃~85℃

额定电压: 100V AC/DC

额定电流: 1A

绝缘电阻: ≥1000MΩ

耐压: 800V AC/minute

2	插针	铜	镀锡	
1	底座	PA66	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE		针座	
料号 PART NO		HC-ZH-5A-M	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比例 SCALE	1:1
X.X ±0.35	X' ±3.00"	单位 UNIT	MM
X.XX ±0.25	X.X' ±2.00"	张数 PART NO	1 OF 1
X.XXX ±0.15	X.XX' ±1.00"	版本 REV	A
制图 DRAW		审核 CHECKED	夏操云
批准 APPROVE		赵亮亮	

