






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE



Footpoint for information only

1. 额定电压/电流: 300V/16A
2. 额定脉冲电压: 4kv
3. 间距/线数范围: 5.0mm/N=2~12P
4. 使用温度范围: -40℃~+85℃

2	接触	铜	镀锡	
1	基座	PA66	灰色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	接线端子	
			料 号 PART NO	HC-JXDZSH-5.0-5P	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
0~3	±0.12	>3~6	±0.18	单 位 UNIT	MM
>6~10	±0.22	>10~18	±0.26	张 数 PART NO	1 OF 1
>18~30	±0.31	>30~50	±0.37	审 核 CHECKED	夏操云
>50~80	±0.57	>120~180	±0.80	版 本 REV	A
>180~250	±0.93	>250~315	±1.05	批 准 APPROVE	赵亮亮
>315~400	±1.60	>400~500	±2.20		
>500	±2.50				