








标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE

| PIN | DIM A | DIM B | DIM C |
|-----|-------|-------|-------|
| 2P  | 10.00 | 6.10  | 2.50  |
| 3P  | 12.50 | 8.60  | 5.00  |
| 4P  | 15.00 | 11.10 | 7.50  |
| 5P  | 17.50 | 13.60 | 10.00 |
| 6P  | 20.00 | 16.10 | 12.50 |
| 7P  | 22.50 | 18.60 | 15.00 |
| 8P  | 25.00 | 21.10 | 17.50 |



## SPECIFICATION

1. Contact resistance:  $\leq 10\text{M}\Omega$
2. Insulation resistance:  $\geq 1000\text{M}\Omega$
3. Rated voltage: 250 V AC DC
4. Rated current: 3.0 A AC DC
5. Withstand Voltage: 1000V AC/minute
6. Temperature Range :  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

RECOMMENDER P.C.B.LAYOUT TOP VIEW  
(COMPONENT SIDE TOLERANCE  $\pm 0.1$ )

|    |     |     |       |     |
|----|-----|-----|-------|-----|
| 2  | 插针  | 铜   | 镀镍锡   |     |
| 1  | 基座  | LCP | 米色    |     |
| 序号 | 品 名 | 材 质 | 电镀/颜色 | 备 注 |



深圳市虹成电子有限公司

|                |                 |
|----------------|-----------------|
| 品 名<br>TITLE   | 针座              |
| 料 号<br>PART NO | HC-XH2. 54-4PLT |

GENERAL TOLERANCES  
(UNLESS SPECIFIED)比 列  
SCALE

1:1

X. xxx  $\pm 0.10$   
X. xx  $\pm 0.20$   
X. x  $\pm 0.30$ 单 位  
UNIT

MM

制 图  
DRAW

AhYe

X. xx°  $\pm 1^{\circ}$   
X. x°  $\pm 3^{\circ}$   
X. °  $\pm 5^{\circ}$ 张 数  
PART NO

1 OF 1

审 核  
CHECKED

夏操云

版 本  
REV

A

批 准  
APPROVE

赵亮亮

