












RoHS



PCB Layout(Pattern Side)



Circuit Diagram

Product No. : TK-580C-□□

型号: 产品类型: 包装方式
1=自锁 -P=编带(非编带, 不启用)
2=无锁

NO.	Operating Type	Part No.	Operating force	Travel
1	Push To Lock	TK-580C-1	180±50gf	2.0±0.3
2	Push No Sound No Lock	TK-580C-2	180±50gf	2.0±0.3

③	Spring		1	SUS	Natural
②	Crochet Needle		1	SUS	Natural
⑤	Terminal		6	Brass	Silvering
④	Reed		2	Phosphorus Copper	Silvering
①	Button		1	PPA	White
⑥	Cover		1	PPA	Black
⑦	Base		1	PPA	Gray

NO.	Name	Number	Qty	Materil	Remarks
design	date	name	BUTTON SWITCH		
Review	date	name	TK-580C-□		
Approved	date	name			

ZHONGDI® Zhongdi Electronic Technology Co., Ltd

angle ±2°
10~30 ±0.30
5~10 ±0.20
~ 5 ±0.10
Drawing number: 1:1 unit mm gage number A4

modify Review Approved Tolerance not specified Proportion 1:1 unit mm gage number A4

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	0.1A
	额定电压 Rated voltage:	DC 30V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
机械性能 Mechanical Properties	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
	机械寿命 Mechanical life:	30,000 cycles Min
	全行程 Total Travel:	2.00±0.30mm
环境性能 Environmental	触发行程 Trigger Travel:	0.90±0.30mm
	工作温度 Operation temperature:	-25℃ ~ +75℃
可靠性特性 Reliability Characteristics	使用湿度 Use humidity:	≤85% RH
	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
应用领域 Application area	手工焊 Manual welding:	≥260℃ 时间 Time 3s
	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪



直流低电阻测试仪




耐电压测试



回流焊



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪					Zhongdi Electronic Technology Co., Ltd				
design		date		name	BUTTON SWITCHS				
Review		date							
Approved		date		model	TK-580C-□				
number:									

modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gap	number	A4	
--------	--------	----------	-------------------------	------------	-----	------	----	-----	--------	----	--