








标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN	DIM A	DIM B	DIM C
2P	10.00	6.10	2.50
3P	12.50	8.60	5.00
4P	15.00	11.10	7.50
5P	17.50	13.60	10.00
6P	20.00	16.10	12.50
7P	22.50	18.60	15.00
8P	25.00	21.10	17.50

RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE ± 0.1)

SPECIFICATION

- 1.Contact resistance: $\leq 10\text{M}\Omega$
- 2.Insulation resistance: $\geq 1000\text{M}\Omega$
- 3.Rated voltage: 250 V AC DC
- 4.Rated current: 3.0 A AC DC
- 5.Withstand Voltage: 1000V AC/minute
- 6.Temperature Range : $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注




深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HC-XH2. 54-6PLT

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1

X. xxx ± 0.10
X. xx ± 0.20
X. x ± 0.30单 位
UNIT

MM

制 图
DRAW

AhYe

X. xx° ± 1°
X. x° ± 3°
X. ° ± 5°张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

版 本
REV

A

批 准
APPROVE

赵亮亮

