




SCHEMATIC



P.C.B LAYOUT

SPECIFICATION

- 1.Rating : DC 20V 6.5A.
- 2.Contact resistance: $\leq 50m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC250V).
- 4.Withstanding voltage: 250VAC .
- 5.Insertion and extraction force: 5-35N
- 5.life test: 5000 cycles.
- 6.Operation temperature range:-25℃~85℃.
- 7.Sign"* "is importance dimension.

					TOLERANCE UNLESS SPECIFIED								
6	包 圆	BRASS	1	Cu/Sn-PLATED	<1.5: ±0.1mm	ANGULAR ±1°							
5	右长针	BRASS	1	Cu/Sn-PLATED	>1.5~5.0: ±0.25mm								
					>5.0: ±0.3mm		NO	DATE	REVISIONS			BY	APPD
4	左短针	BRASS	1	Cu/Sn-PLATED	TITLE: XLR, Femail				UNIT : MM	ROHS	DWN		
3	弯 针	BRASS	1	Cu/Sn-PLATED	MODEL: DIN-326A				SCALE: 1:1	COMPLIANT	CHK'D		
2	后 盖	PBT	1	BLACK	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司						APPD		
1	基 座	PBT	1	BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL:		 	REV :A0	