




7		8		9	
标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日期 DATE	核 准 APPROVE	
	Pin	DIM A	DIM B	DIM C	
	2	4.50	1.50	3.60	
	3	6.00	3.00	5.10	
	4	7.50	4.50	6.60	
	5	9.00	6.00	8.10	
	6	10.50	7.50	9.60	
	7	12.00	9.00	11.10	
	8	13.50	10.50	12.60	
	9	15.00	12.00	14.10	
	10	16.50	13.50	15.60	
	11	18.00	15.00	17.10	
	12	19.50	16.50	18.60	
	13	21.00	18.00	20.10	
	14	22.50	19.50	21.60	
	15	24.00	21.00	23.10	
	16	25.50	22.50	24.60	

技术要求：
适应基板厚度：1.2mm~1.6mm
温度范围：-25℃~85℃
额定电压：100V AC/DC
额定电流：1A
绝缘电阻：≥1000MΩ
耐 压：800V AC/minute

2	插针	铜	镀锡	
1	底座	PA66	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE		针座	
料号 PART NO		HC-ZH-6A-M	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1
X.X ±0.35	X' ±3.00"	单位 UNIT	MM
X.XX ±0.25	X.X' ±2.00"	张数 PART NO	1 OF 1
X.XXX ±0.15	X.XX' ±1.00"	版本 REV	A
		制图 DRAW	AhYe
		审核 CHECKED	夏操云
		批准 APPROVE	赵亮亮

