





标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

1. 额定电压/电流: 300V/16A
2. 额定脉冲电压: 4kv
3. 线径范围(硬线&软线)
(mm²/AWG): 0.5...2.5/20...12
4. 间距/线数范围: 5.0/N=2~12P
5. 剥线长度: 10-12mm
6. 使用温度范围: -40℃~+85℃



2	接触	铜	镀镍锡	
1	基座	PA66	灰色	
序号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司			品 名	接线端子			
				TITLE				
				料 号	HC-JXDZRP-5.0-2P			
				PART NO				
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 列	1 : 1				
			SCALE					
0~3	±0.12	>3~6	±0.18	单 位	MM	制 图	AhYe	
>6~10	±0.22	>10~18	±0.26	UNIT				
>18~30	±0.31	>30~50	±0.37	张 数	审 核	夏操云		
>50~80	±0.57	>120~180	±0.80	PART NO	CHECKED			
>180~250	±0.93	>250~315	±1.05	版 本	批 准	赵亮亮		
>315~400	±1.60	>400~500	±2.20	REV			APPROVE	
>500	±2.50			A				