






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE
PIN数	A±0.15	B±0.15	C±0.15	D±0.15
2P	4.30	1.00	3.25	2.65
3P	5.30	2.00	4.25	3.65
4P	6.30	3.00	5.25	4.65
5P	7.30	4.00	6.25	5.65
6P	8.30	5.00	7.25	6.65
7P	9.30	6.00	8.25	7.65
8P	10.30	7.00	9.25	8.65





3D View



Specifications:

1. Rated Voltage : 50V AC/DC
2. Rated Current : 1A AC,DC
3. Withstand Voltage : 200V AC/minute
4. Contact Resistance : 50mΩ(MAX.)
5. Insulation Resistance : 100MΩ(MIN.)
6. Storage Temperature Range: -40°C~+85°C;
7. Operation Temperature Range: -25°C~+70°C;

RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.1)

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE		针座		
料号 PART NO		HC-SH1.0-2PWT		
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1	制图 DRAW
X. xxx ±0.05		单位 UNIT	MM	审核 CHECKED
X. xx ±0.15		张数 PART NO	1 OF 1	夏操云
X. x ±0.25		版本 REV	A	批准 APPROVE
ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°		赵亮亮		

