







RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ± 0.05

NOTES:


1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK

2.TERMINAL/GROUND PLANE:PHOSPHOR BRONZE

PLATING:10u" GOLD IN CONTACT AREA, MATTE TIN ON TAIL.

3.CODING INFORMATION: LXW232-xxxS-B3R-02

WATER CODE
PACKING: R: CARRIER REEL
MATERIAL: 3:LCP
COLOR: B:BLACK
S:SOCKET
PIN
PLATING: G:GOLD FLASH 2:3u" GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
3:5u" GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
4:10u" GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
5:15u" GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
6:30u" GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
0.5 BTB
HIGHLY: 32---3.25H
LXWCONN BTB CONNECTOR SERIES



NO. of contacts	Dimensions		
	A.	B.	C.
40	21.28	20.13	0.10
80	41.28	40.13	0.10
120	61.28	60.13	0.15
160	81.28	80.13	0.15
200	101.28	100.13	0.15

LXW 连兴旺电子(深圳)有限公司
LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

制图 (DR):	Kavin	品名(TITLE):	0.5mm DOUBLE ROW BTB SOCKET H3.25
审核 (CHKD):		料号(PART NO.):	LXW232-XXXS-B3R-02 (QSE)
核准 (APPD):		比例(SCALE):	1:8
		单位(UNITS):	mm
		张数(SHEET):	1 OF 1
		图幅(SIZE):	A4



修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

版本 (REV)	A
一般公差 GENERAL TOLERANCE	± 0.25
.X	± 0.20
.XX	± 0.10
.XXX	± 0.05
ANGLES	$\pm 1^\circ$