



RECOMMENDED P.C.B. LAYOUT
GENERAL TOLERANCE: ±0.05

说明:

1. 材质:

胶芯:LCP, UL94V-0; COLOR:BLACK

端子:C5191

外壳:C2680

2. 电镀说明:

端子:接触区域镀金G. F

焊锡区域镀锡

全部区域镀镍

外壳:表面镀镍

3. 性能说明:

1) 电压:150V AC RMS.

2) 额定电流:1.5A.

3) 接触电阻:40mΩ Max.

4) 绝缘电阻:500MΩ MIN.

5) 绝缘耐压:1000V AC.

6) 工作温度:-40°C T0 +80°C.

7) 耐久性:500 Mating Cycles MIN.

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

DATE:

WUJIANBO

2024-06-21

深圳市灿科盟实业有限公司
CKM TECHNOLOGY CHANKLEMENT INDUSTRY CO., LTD

TITLE:

RJ45-8P/8C SMT 沉板4.2 带屏蔽 无灯 无弹

PART. NO. R-RJ45M08P-B007

UNIT	mm	SCALE	Free	REV.	A	HW04	1/1
FILE NO.	CKmtw-RJ45-0335						