





1	2		3	4	5	6	7	8	
High photosynthesis (H)	The female seat height (H1)	The male seat height (H2)	Insertion height (H3)		REV	ECN	DESCRIPTION	MDF' D	DATE
3.0	2.2	0.8	1.6		1.0	/	新发行	fan Z. J.	2021-07-08
3.5	2.2	1.3	1.6						
4.0	3.0	1.0	1.9						
4.5	3.5	1.0	1.9						
5.0	3.0/4.0	2.0/1.0	1.9						
5.5	3.5/4.5	2.0/1.0	1.9						
6.0	4.0	2.0	1.9						
6.5	4.5	2.0	1.9						
7.0	3.0	4.0	1.9						
7.5	3.5	4.0	1.9						
8.0	4.0	4.0	1.9						
8.5	4.5	4.0	1.9						



ASSEMBLY

REV	ECN	DESCRIPTION	MDF' D	DATE
1.0	/	新发行	fan Z. J.	2021-07-08

NO. of Contacts	Dimension (mm)				
	A±0.10	B±0.10	C±0.10	D±0.10	E±0.10
6	4.20	1.00	2.90	2.00	
8	4.70	1.50	3.40	2.50	
10	5.20	2.00	3.90	3.00	
12	5.70	2.50	4.40	3.50	
14	6.20	3.00	4.90	4.00	
16	6.70	3.50	5.40	4.50	
18	7.20	4.00	5.90	5.00	
20	7.70	4.50	6.40	5.50	
22	8.20	5.00	6.90	6.00	
24	8.70	5.50	7.40	6.50	
26	9.20	6.00	7.90	7.00	
28	9.70	6.50	8.40	7.50	
30	10.20	7.00	8.90	8.00	
32	10.70	7.50	9.40	8.50	
34	11.20	8.00	9.90	9.00	
36	11.70	8.50	10.40	9.50	
38	12.20	9.00	10.90	10.00	
40	12.70	9.50	11.40	10.50	
42	13.20	10.00	11.90	11.00	
44	13.70	10.50	12.40	11.50	
46	14.20	11.00	12.90	12.00	
48	14.70	11.50	13.40	12.50	
50	15.20	12.00	13.90	13.00	
52	15.70	12.50	14.40	13.50	
54	16.20	13.00	14.90	14.00	
56	16.70	13.50	15.40	14.50	
58	17.20	14.00	15.90	15.00	
60	17.70	14.50	16.40	15.50	
62	18.20	15.00	16.90	16.00	
64	18.70	15.50	17.40	16.50	
66	19.20	16.00	17.90	17.00	
68	19.70	16.50	18.40	17.50	
70	20.20	17.00	18.90	18.00	
72	20.70	17.50	19.40	18.50	
74	21.20	18.00	19.90	19.00	
76	21.70	18.50	20.40	19.50	
78	22.20	19.00	20.90	20.00	
80	22.70	19.50	21.40	20.50	
82	23.20	20.00	21.90	21.00	
84	23.70	20.50	22.40	21.50	
86	24.20	21.00	22.90	22.00	
88	24.70	21.50	23.40	22.50	
90	25.20	22.00	23.90	23.00	
92	25.70	22.50	24.40	23.50	
94	26.20	23.00	24.90	24.00	
96	26.70	23.50	25.40	24.50	
98	27.20	24.00	25.90	25.00	
100	27.70	24.50	26.40	25.50	



P.B.C LAYOUT

5001-BTB 0508- ** M R -00
 The standby
 PACKING: R: REEL
 MALE
 PIN
 HEIGHT: 08-0.8H; 10-1.0H
 13-1.3H; 20-2.0H
 0.5BTB
 JM CONN BTB CONNECTOR SERIES

.X ±0.20	.X° ±1.0°
.XX ±0.10	.XX° ±0.5°
.XXX ±0.05	.XXX° ±0.2°
SCALE 1:1	UNIT mm
PAGE: 1/1	REV: 1.0

深圳市文章济美科技有限公司


Part Name: B T B 0.5双排 公头	Approved:
Part No.: 5001-BTB0508- **MR-00-B	Checked:
Title:	Material: ---
Drawing No.: G8BTC0006	Date: 2021-07-08

No.	品名	数量	材料	表面处理	备注
1	端子	PIN数	C5191 H	全金Flash 0.6U"	
2	本体	1	PANT 黑色		
3	CAP	1	PANT 黑色		

A
B
C
D
E
F





A
B
C
D
E
F

1	2		3	4	5	6	7	8	
High photosynthesis (H)	The female seat height (H1)	The male seat height (H2)	Insertion height (H3)		REV	ECN	DESCRIPTION	MDF' D	DATE
3.0	2.2	0.8	1.6		1.0	/	新发行	fan Z. J.	2021-07-08
3.5	2.2	1.3	1.6						
4.0	3.0	1.0	1.9						
4.5	3.5	1.0	1.9						
5.0	3.0/4.0	2.0/1.0	1.9						
5.5	3.5/4.5	2.0/1.0	1.9						
6.0	4.0	2.0	1.9						
6.5	4.5	2.0	1.9						
7.0	3.0	4.0	1.9						
7.5	3.5	4.0	1.9						
8.0	4.0	4.0	1.9						
8.5	4.5	4.0	1.9						



ASSEMBLY

NO. of Contacts	Dimension (mm)				
	A±0.10	B±0.10	C±0.10	D±0.10	E±0.10
6	4.20	1.00	2.90	2.06	
8	4.70	1.50	3.40	2.56	
10	5.20	2.00	3.90	3.06	
12	5.70	2.50	4.40	3.56	
14	6.20	3.00	4.90	4.06	
16	6.70	3.50	5.40	4.56	
18	7.20	4.00	5.90	5.06	
20	7.70	4.50	6.40	5.56	
22	8.20	5.00	6.90	6.06	
24	8.70	5.50	7.40	6.56	
26	9.20	6.00	7.90	7.06	
28	9.70	6.50	8.40	7.56	
30	10.20	7.00	8.90	8.06	
32	10.70	7.50	9.40	8.56	
34	11.20	8.00	9.90	9.06	
36	11.70	8.50	10.40	9.56	
38	12.20	9.00	10.90	10.06	
40	12.70	9.50	11.40	10.56	
42	13.20	10.00	11.90	11.06	
44	13.70	10.50	12.40	11.56	
46	14.20	11.00	12.90	12.06	
48	14.70	11.50	13.40	12.56	
50	15.20	12.00	13.90	13.06	
52	15.70	12.50	14.40	13.56	
54	16.20	13.00	14.90	14.06	
56	16.70	13.50	15.40	14.56	
58	17.20	14.00	15.90	15.06	
60	17.70	14.50	16.40	15.56	
62	18.20	15.00	16.90	16.06	
64	18.70	15.50	17.40	16.56	
66	19.20	16.00	17.90	17.06	
68	19.70	16.50	18.40	17.56	
70	20.20	17.00	18.90	18.06	
72	20.70	17.50	19.40	18.56	
74	21.20	18.00	19.90	19.06	
76	21.70	18.50	20.40	19.56	
78	22.20	19.00	20.90	20.06	
80	22.70	19.50	21.40	20.56	
82	23.20	20.00	21.90	21.06	
84	23.70	20.50	22.40	21.56	
86	24.20	21.00	22.90	22.06	
88	24.70	21.50	23.40	22.56	
90	25.20	22.00	23.90	23.06	
92	25.70	22.50	24.40	23.56	
94	26.20	23.00	24.90	24.06	
96	26.70	23.50	25.40	24.56	
98	27.20	24.00	25.90	25.06	
100	27.70	24.50	26.40	25.56	



P.B.C LAYOUT

5001-BTB 0522-**FR-00
 The standby
 PACKING: R: REEL
 FEMALE
 PIN
 HEIGHT: 22-2.2H; 30-3.0H
 35-3.5H; 40-4.0H
 45-4.5H.
 0.5BTB
 JM CONN BTB CONNECTOR SERIES


.X ±0.20	.X° ±1.0°
.XX ±0.10	.XX° ±0.5°
.XXX ±0.05	.XXX° ±0.2°
SCALE 1:1	UNIT mm
PAGE: 1/1	REV: 1.0

深圳市文章济美科技有限公司

Part Name: BTB 0.5双排 母座	Approved:
Part No.: 5001-BTB0522-**FR-00-B	Checked:
Title:	Material: ---
Drawing No.: G8BTC0005	Date: 2021-07-08


No.	品名	数量	材料	表面处理	备注
1	端子	PIN数	C5191 H	全金Flash 0.6U"	
2	本体	1	PANT 黑色		
3	CAP	1	PANT 黑色		

Top edge width 16 and 24mm



PULL OUT DIRECTION



Top edge width 32 and 44mm



PULL OUT DIRECTION

NOTE:

- 1.10 Sprocket hole pitch cumulative tolerance ± 0.20 .
2. Carrier camber is within 1mm in 100mm.
3. Material: black conductive polystyrene alloy.
4. Material Thickness: 0.3 ± 0.05 mm.
5. All dimensions meet EIA-481-B requirements.
6. 5000pcs Pef Reel.
7. For tape width(dim W)16 and 24mm pilot holes are provided on one sides.
For tape width(dim W)32, 44 and 56mm pilot holes are provided on both sides.



PIN NO.	W	C	PCS /REEL	REEL/CARTON	SUM(PCS)
4PIN~20PIN	16	-	1000	15	15000
22PIN~52PIN	24	-	1000	10	10000
54PIN~70PIN	32	28.4	1000	8	8000
72PIN~100PIN	44	40.4	1000	6	6000

REV	DESCRIPTION	SIGNATURE	DATE

深圳市文章济美科技有限公司

一般公差 GENERAL TOLERANCE .X ±0.10 .XX ±0.05 .XXX ±0.02 ANGLES ±1°	制图 (DR): Z. J. Fan 2021.08.28	品名 (TITLE): BOARD to BOARD EMBOSSED TAPE PACKING
版本 (REV) A	审核 (CHKD):	料号 (PART NO): 5001-BTB05**-**MR-00-B 比例 (SCALE): 1:1
核准 (APPD):	单位 (UNITS): mm	张数 (SHEET): 1 OF 1 图幅 (SIZE): A4

