






Taping Reel



Embossed Carrier Taping



PWB mounting hole for reference



pole 1-throw (N . O

Specifications

Rating	50 μ A 3 V DC to 10 mA 5 V DC (Resistive load)
Contact Resistance	500 m Ω max. (Initial)
Insulation Resistance	100 M Ω min. (at 100 V DC for 1 minute)
Dielectric Withstanding Voltage	100 V AC (50 Hz or 60 Hz) for 1 minute
Operating Force	390 mN max.
Mounting Height	1.7 mm
Poles and Throws	1-pole 1-throw
Full Travel (Pushing distance)	3.2 mm (2.15 mm)
Operating Life	50,000 cycles min.
Temperature Range	-10 $^{\circ}$ C to +70 $^{\circ}$ C (Standard), -40 $^{\circ}$ C to +85 $^{\circ}$ C (Automotive)
Heat Resistance	+85 $^{\circ}$ C for 96 hours
Low Temperature Resistance	-40 $^{\circ}$ C for 96 hours
Humidity Resistance	+60 $^{\circ}$ C 90 % to 95 % RH for 96 hours
Minimum Quantity/Packing Unit	2,500 pcs. Embossed Taping (Reel Pack)
Quantity/Cartron	15,000 pcs.

GENERAL TOLERANCE		制 图 DRAWING	黄彬 2018.01.15		料 号 PART NO.	HX KFC-ESE31L11T-L	版 本 REV.	A
X.±0.25	X.±2°		审 核 CHECK	张伟 2018.01.15	品 名 TITLE	限位开关	页 次 SHEET	1/1
.X±0.20	.X'±1°	核 准 APPROVAL			罗小春 2018.01.15	客户料号 CUTM. NO.		
.XX±0.15	.XX'±0.5°		单 位 UNITS	MM		比 例 1:1	 韩下® 深圳市韩下电子有限公司	
.XXX±0.10	.XXX±0.5°							