



备注:

1. 材质:

- 1.1 端子: C5191R-EH, T=0.15mm.
- 1.2 胶芯: LCP+30%GF; 颜色: 黑色
- 1.3 外壳: SUS304R-1/2H, T0.30mm

2. 电镀:

- 2.1 端子: 电镀镍底50u"Min. (焊接区域) 锡脚 电镀亮锡80u"Min.
- 2.2 外壳: 电镀镍底50u"Min.



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

Product Edge

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: TYPE-C 16P母座 四脚全贴 带柱 不锈钢带弹			
DRAWN: HCY	DATE: 2019-08-02	PART. NO.	U-USBTM16P-F001		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-usb3.1-0077	REV.	A