




G-Switch USB-C Specification:

1. Current rated: 5A on vbus/1.25A on vconn/0.25A on other
2. Withstanding voltage: 100V AC/minute
3. Contact resistance: 40mΩ Max
4. Insulation resistance: 100MΩ Min
5. Operating temperature: -40°C ~ +85°C
6. Mating force: 5N~20N
7. Unmating force: 8N~20N
8. Durability cycle: 10,000 cycles
9. Data transmission rate up to 5Gbps
10. Compliant with: IEC62680-1-3

USB IF TID:13209

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SBU1	VBUS	RX2-	RX2+	GND
First	Second	Second	First	Second	Second	Second	Second	First	Second	Second	First
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND	RX1+	RX1-	VBUS	SBU2	D-	D+	CC2	VBUS	TX2-	TX2+	GND
First	Second	Second	First	Second	Second	Second	Second	First	Second	Second	First



PCB REFERENCE DIAGRAM
TOLERANCE:±0.05

1	SHELL	STAINLESS STEEL 304	NI30u"MIN PLATED
2	GND PLATE	STAINLESS STEEL 301	NI30u"MIN PLATED
3	MID PLATE	STAINLESS STEEL 301	-
4	HOUSING	HIGH TEMPERATURE PLASTIC	LCP BLACK UL 94V-0
5	TERMINALS	COPPER ALLOY C7025	Au1u"MIN PLATING ON CONTACT AREA G/F MIN PLATING ON CONTACT AREA
NO.	PARTS	MATERIAL	REMARKS



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise General Tolerance:
X. ±0.40
X.x ±0.30
X.xx ±0.20
X.xxx ±0.10
X* ±5°

Title: Horizontal Type-C 24P Female SMT
Mid-Mount 1.0 CH=0.58 L=7.9mm

Molde Code: GT-USB-9007B

DRAWN	CHECKED	APPROVED	DATE
Wu	Xia	Chen	2025.01.31



REV: A0 SHEET: 1/1

A

B

D

E

A

B

D

E

品赞电子(东莞)有限公司

品赞电子(东莞)有限公司