








版次 (Rev)	变更摘要 (Change the abstract)	日期 (Date)	序号 No.	品名 TITLE	材质 MATERIAL
0	新产品发行	2016/9/25	①	1.0- E型卧式WTB胶芯	LCP UL94V-0 自然色
1	客诉公母座对配保持力偏小, 设变胶芯两侧加胶凸点	2018/10/30	②	1.0- E型立式WTB端子	铜合金/表面镀锡
2	料号变更	2024/8/30	③	1.0- E型卧式WTB焊片	铜合金/表面镀锡
			④	1.0- E型立式吸盖	LCP UL94V-0 自然色



SECTION A-A



CKT	DIM A	DIM B	DIM C
2	1.00	2.50	4.00
3	2.00	3.50	5.00
4	3.00	4.50	6.00
5	4.00	5.50	7.00
6	5.00	6.50	8.00
7	6.00	7.50	9.00
8	7.00	8.50	10.00
9	8.00	9.50	11.00
10	9.00	10.50	12.00
11	10.00	11.50	13.00
12	11.00	12.50	14.00
13	12.00	13.50	15.00
14	13.00	14.50	16.00
15	14.00	15.50	17.00
16	15.00	16.50	18.00
17	16.00	17.50	19.00
18	17.00	18.50	20.00
19	18.00	19.50	21.00
20	19.00	20.50	22.00
22	21.00	22.50	24.00
24	23.00	24.50	26.00
26	25.00	26.50	28.00

- 技术指标:
- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 - 温度范围: -25°C ~ 85°C.
 - 额定电压: 50V, AC.
 - 接触电阻: ≤ 0.02Ω.
 - 绝缘电阻: ≥ 100MΩ.
 - 额定电流:
 - 适用电线型号: a. AWG#28: 1.0A (per pin)
 - b. AWG#30: 1.0A (per pin)
 - c. AWG#32: 0.8A (per pin)



一般公差 (TOLERANCE)
 X ± 0.50 .XX ± 10
 X ± 0.20 .XXX ± 0.5
 ANGLES ± 1°

广东国连电子有限公司
 GUANGDONG GUOLIAN ELECTRONICS CO., LTD

品名 (TITLE) SH1.0立贴 制图 (DR)

料号 (DWG.NO) 1.0-P-NPB-*** 校对 (CHKD)

比例 (SCALE) 单位 (UNITS) mm 审核 (APPD)

张数 (SHEET) 1 OF 1 SIZE A4 REV A