






A B C D E F

版次	变更摘要	日期
0	新产品发行	2017/11/03
1	更改焊片预断位置, 提高生产效率	2021/07/14
2	加高焊片总高度, 提高共面度的良率	2022/9/5
3	料号变更	2024/8/30


序号	品名	材质
①	1.5- L型立式WTB胶芯	LCP UL94V-0 自然色 红色
②	1.5- L型立式WTB端子	铜合金/表面镀锡/ 表面镀金
③	1.5- L型立式WTB焊片	铜合金/表面镀锡
④	1.5- L型立式WTB吸盖	LCP UL94V-0 自然色



With Cover

CKT	DIM A	DIM B	DIM C
2	1.50	6.00	3.65
3	3.00	7.50	5.15
4	4.50	9.00	6.65
5	6.00	10.50	8.15
6	7.50	12.00	9.65
7	9.00	13.50	11.15
8	10.50	15.00	12.65
9	12.00	16.50	14.15
10	13.50	18.00	15.65
11	15.00	19.50	17.15
12	16.50	21.00	18.65
13	18.00	22.50	20.15
14	19.50	24.00	21.65
15	21.00	25.50	23.15
16	22.50	27.00	24.65
17	24.00	28.50	26.15
18	25.50	30.00	27.65
19	27.00	31.50	29.15
20	28.50	33.00	30.65

- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -25° C~85° C.
 3. 额定电压: 100V, AC/DC.
 4. 接触电阻: ≤0.02Ω.
 5. 绝缘电阻: ≥500MΩ.
 6. 额定电流: 1A , AC/DC.



广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO., LTD

品名 (TITLE) ZH1.5立贴
料号 (DWG.NO) ZH1.5-NAB-***

比例 (SCALE) 单位 (UNITS) mm

制图 (DR) 校对 (CHKD) 审核 (APPD)

张数 (SHEET) 1 OF 1 SIZE A4 REV A

一般公差 (TOLERANCE)
X ±.50 .XX ±.10
X ±.20 .XXX ±.05
ANGLES ±1°

A B C D E F