









版次 (edition)	变更摘要 (Change the abstract)	日期 (Date)	序号 (NO.)	品名 (TITLE)	材质 (material)
0	新产品发行 (New product release)	2016/9/25	①	1.0-E型卧式WTB胶芯	LCP UL94V-0 自然色
1	客诉公母座对配保持力偏小, 设变胶芯两侧加胶凸点	2018/10/30	②	1.0-E型卧式WTB端子	铜合金/表面镀锡
2	料号更新	2024/8/30	③	1.0-E型卧式WTB焊片	铜合金/表面镀锡



CKT	DIM A	DIM B	DIM C
2	1.00	2.50	4.00
3	2.00	3.50	5.00
4	3.00	4.50	6.00
5	4.00	5.50	7.00
6	5.00	6.50	8.00
7	6.00	7.50	9.00
8	7.00	8.50	10.00
9	8.00	9.50	11.00
10	9.00	10.50	12.00
11	10.00	11.50	13.00
12	11.00	12.50	14.00
13	12.00	13.50	15.00
14	13.00	14.50	16.00
15	14.00	15.50	17.00
16	15.00	16.50	18.00
17	16.00	17.50	19.00
18	17.00	18.50	20.00
19	18.00	19.50	21.00
20	19.00	20.50	22.00
22	21.00	22.50	24.00
24	23.00	24.50	26.00
26	25.00	26.50	28.00

技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
- 温度范围: -25° C~85° C.
- 额定电压: 50V, AC/DC.
- 接触电阻: ≤0.02Ω.
- 绝缘电阻: ≥100MΩ.
- 额定电流:
 - a. AWG#28:1.0A(per pin)
 - b. AWG#30:1.0A(per pin)
 - c. AWG#32:0.8A(per pin)



广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO., LTD

品名 (TITLE)	SH1.0卧贴	制图 (DR)
料号 (DWG. NO)	1.0-Q-NPWB-***	校对 (CHKD)
比例 (SCALE)	mm	审核 (APPD)
单位 (UNITS)	mm	张数 (SHEET)
		1 OF 1
		SIZE A4
		REV A

一般公差 (TOLERANCE)
 X ±.50 .XX ±.10
 X ±.20 .XXX ±.05
 ANGLES ±1°