







180°






90°



90°

带定位



标记	说 明	签名	日期
△			
△			
△			

技术参数 SPECIFICATION

间距: 2.0

Pitch: 2.0

工作温度: -25℃ ~ +85℃

Working temperature: -25℃ ~ +85℃

额定电压: 250V DC/AC (有效值)

Voltage rating: 250V DC/AC (rms)

额定电流: 5.0A

Current rating: 5.0A

接触电阻: ≤0.02Ω

Contact resistance: ≤0.02Ω

绝缘电阻: ≥1000MΩ

Insulation resistance: ≥1000MΩ


耐压: 1500V AC (有效值)

Withstand voltage: 1500V AC (rms)

焊接温度: 260 ± 5℃

Soldering temperature: 260 ± 5℃

印制板开孔尺寸 (±0.1)



9	9PIN	9PIN	9PIN	16	20	17					
8	8PIN	8PIN	8PIN	14	18	16	16PIN	16PIN	16PIN	30	34
7	7PIN	7PIN	7PIN	12	16	15	15PIN	15PIN	15PIN	28	32
6	6PIN	6PIN	6PIN	10	14	14	14PIN	14PIN	14PIN	26	30
5	5PIN	5PIN	5PIN	8	12	13	13PIN	13PIN	13PIN	24	28
4	4PIN	4PIN	4PIN	6	10	12	12PIN	12PIN	12PIN	22	26
3	3PIN	3PIN	3PIN	4	8	11	11PIN	11PIN	11PIN	20	24
2	2PIN	2PIN	2PIN	2	6	10	10PIN	10PIN	10PIN	18	22
极数	180°	90°	90° 带定位	A	B	极数	180°	90°	90° 带定位	A	B
产品规格				尺寸 (mm)		产品规格				尺寸 (mm)	

L>10	±0.3	③							
6<L≤10	±0.2	②	基座	1			PA46		米黄色
L≤6	±0.1	①	插针	n			H62		镀锡
角度	±3°	序号	名称	数量	对应端子号	材	质	备	注

东莞市高钱达电子科技有限公司

设计		日期		名称	WAF2.0*xxP直插带扣				
审核		日期			7700-xxK1-TH (180°)				
核准		日期		页码	1/1	版本			
比例	1:1	视图	单位	mm	图面编号				