





D	E	F			
版次	变更摘要	日期	序号	品名	材质
0	新产品发行	2017/12/02			
1	修改产品焊接面尺寸与焊位尺寸	2019/04/29			
2	改善公头对配胶芯卡扣开裂	2019/07/30	①	2.50 M型立式WTB胶芯	LCP UL94V-0 本色
3	料号更新	2024/11/13			



WITH COVER



技术指标：



1. 塑件表面应光洁、无毛边、无明显收缩、
缺陷、裂纹等现象。
 2. 工作温度: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
 3. 适用线规: AWG#28~#22。
 4. 额定电压: 250V DC/AC(rms)。
 5. 额定电流: 3.0A。
 6. 接触电阻: $\leq 20\text{m}\Omega$ 。
 7. 耐压值: 1000V AC/minute。
 8. 绝缘电阻: $\geq 1000\text{MO}$ 。

CKT	DIM A	DIM B	DIM C
2	2.50	7.50	10.00
3	5.00	10.00	12.50
4	7.50	12.50	15.00
5	10.00	15.00	17.50
6	12.50	17.50	20.00
7	15.00	20.00	22.50
8	17.50	22.50	25.00
9	20.00	25.00	27.50
10	22.50	27.50	30.00
11	25.00	30.00	32.50
12	27.50	32.50	35.00
13	30.00	35.00	37.50
14	32.50	37.50	40.00
15	35.00	40.00	42.50
16	37.50	42.50	45.00



广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO., LTD.

品名 (TITLE) XH2.5立贴		制图 (DR)			
		校对 (CHKD)			
料号 (DWG.NO) XH2.5-NAB-***		审核 (APPD)			
比例 (SCALE) mm	单位 (UNITS) mm	 	张数 (SHEET) 1 OF 1	SIZE A4	REV A
E		E			



2P 结构

RoHS

一般公差 (TOLERANCE)
X. $\pm .50$.XX $\pm .10$
.X $\pm .20$.XXX $\pm .05$
ANGLES $\pm 1^\circ$

A

B

C

D

11

1