



NOTES:
Current Rating:3.0AMP
Contact Resistance:20mΩ max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ min
Operation Temperature:−40℃ to +105℃

Contact Material:Brass
Contact plating:
1u"Min Gold Plating Over All
50u"Min Nickel Underplating Over All
Insulator Material:PA9T+30%GF(UL94V−0)
Packaging: Reel





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



MTP125-2205M(H=20.0,B=8.0,W=7.5)

No.of Pins per
Row: 01~40



Dimension antitheses list		
ITEM	D	W
Standard	1.20	7.50
Alternate		

X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.			
.X ± 0.20	.X° ± 2°	MAT'L					
.XX ± 0.10	.XX° ± 1°	FINISH	PART NO.(INTENDED USE)	TITLE:			
.XXX ± 0.05	.XXX° ± 0.5°		APPD: SUNNY	MTP125-2205M(H=20.0,B=8.0,W=7.5)			
PIN HEADER CONNECTOR			CHKD: LISA	DWG NO.:			
			DR: ZOE 2006-11-28				
				SCALE	SHEET	REV.	
				1 / 1	1 / 1	A	