



REV.	ECN. NO.	APPD.
A		

NOTES:
Rated Current:2.0AMP.
Contact Resistance:20mΩ Max.
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min.
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:PA9T+30%G.F UL94V-0 BK





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

MTP220-12XXR2

No.of Pins per
Row: 01~40



Dimension antitheses list			
ITEM	A	B	D
Standard	2.80	4.00	0.75
Alternate			

X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.			
.X ± 0.20	.X° ± 2°	MAT'L					
.XX ± 0.10	.XX° ± 1°	FINISH	PART NO.(INTENDED USE)	TITLE: MTP220-12XXR2			
.XXX ± 0.05	.XXX° ± 0.5°		APPD: SUNNY	DWG NO.:			
PIN HEADER CONNECTOR		Q'TY	CHKD: LISA	 SCALE1 / 1SHEET1 / 1REV.A			
			DR: ZOE 2006-11-28				