







REV.	ECN. NO.	APPD.
A		
序号	品名	材质
①	0.3插盖胶芯 (H1.0)	LCP UL94V-0 本色
②	0.3插盖端子 (H1.0)	铜合金/表面镀金
③	0.3插盖后盖 (H1.0)	LCP UL94V-0 黑色
④	0.3插盖垫片 (H1.0)	铜合金/表面镀锡



CKT	D1MA	D1MB	D1MC	D1MD
13	3.60	4.26	5.46	3.00
15	4.20	4.86	6.06	3.60
17	4.80	5.46	6.66	4.20
19	5.40	6.06	7.26	4.80
21	6.00	6.66	7.86	5.40
23	6.60	7.26	8.46	6.00
25	7.20	7.86	9.06	6.60
27	7.80	8.46	9.66	7.20
29	8.40	9.06	10.26	7.80
31	9.00	9.66	10.86	8.40
33	9.60	10.26	11.46	9.00
35	10.20	10.86	12.06	9.60
37	10.80	11.46	12.66	10.20
39	11.40	12.06	13.26	10.80
41	12.00	12.66	13.86	11.40
43	12.60	13.26	14.46	12.00
45	13.20	13.86	15.06	12.60
47	13.80	14.46	15.66	13.20
49	14.40	15.06	16.26	13.80
51	15.00	15.66	16.86	14.40
53	15.60	16.26	17.46	15.00
55	16.20	16.86	18.06	15.60
57	16.80	17.46	18.66	16.20
59	17.40	18.06	19.26	16.80
61	18.00	18.66	19.86	17.40
63	18.60	19.26	20.46	18.00
65	19.20	19.86	21.06	18.60
67	19.80	20.46	21.66	19.20
69	20.40	21.06	22.26	19.80
71	21.00	21.66	22.86	20.40

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -55° C~85° C.
3. 接触电阻: ≤40mΩ (DC20mA最大电压/10mA最大电流).
4. 额定电压: 30V AC.
5. 额定电流: 0.2A DC.
6. 绝缘电阻: ≥50MΩ (DC500V).
7. 产品料号:

XW03102—XX X X

NO. OF CKT (产品PIN数)

Plating (电镀方式)

- 1: 端子全金 (G/F OVERALL)
- 6: 端子点镀金

Packing (包装方式)

- T: TUBE管装
- R: TAPE & REEL卷装

X.	±0.30	X°	±5°	UNITS	mm
.X	±0.20	.X°	±2°	MAT'L	
.XX	±0.10	.XX°	±1°		
.XXX	±0.05	.XXX°	±0.5°	FINISH	

NAME (INTENDED USE)		PART NO. (INTENDED USE)		TITLE:	
FPC CONNECTOR				MINTRON CO., LTD.	
DR.	ZOE	APPD.	SUNNY	FPC0.3 掀盖卧式下接 (H=1.0)	
CHKD.	LISA	DWG NO.:	XW03102-XXXX		
2015-1-28		SCALE	1/1	SHEET	1/1
		REV.	A		