







REV.	ECN. NO.	APPD.
A		
序号	品名	材质
①	1.0K型胶芯 (02.5)	LCP UL94V-0 本色 (02.5)
②	1.0K型下接端子 (02.5)	磷青铜/表面镀锡
③	1.0K型防式百盖 (02.5)	LCP UL94V-0 黑色 (02.5)
④	1.0K型防式弹片 (02.5)	黄铜/表面镀锡



KIT	DIM A	DIM B	DIM C
4	3.00	5.03	11.00
5	4.00	6.03	12.00
6	5.00	7.03	13.00
7	6.00	8.03	14.00
8	7.00	9.03	15.00
9	8.00	10.03	16.00
10	9.00	11.03	17.00
11	10.00	12.03	18.00
12	11.00	13.03	19.00
13	12.00	14.03	20.00
14	13.00	15.03	21.00
15	14.00	16.03	22.00
16	15.00	17.03	23.00
17	16.00	18.03	24.00
18	17.00	19.03	25.00
19	18.00	20.03	25.00
20	19.00	21.03	27.00
21	20.00	22.03	28.00
22	21.00	23.03	29.00
23	22.00	24.03	30.00
24	23.00	25.03	31.00
25	24.00	26.03	32.00
26	25.00	27.03	33.00
27	26.00	28.03	34.00
28	27.00	29.03	35.00
29	28.00	30.03	36.00
30	29.00	31.03	37.00
31	30.00	32.03	38.00
32	31.00	33.03	39.00
33	32.00	34.03	40.00
34	33.00	35.03	41.00
35	34.00	36.03	42.00
36	35.00	37.03	43.00
37	36.00	38.03	44.00
38	37.00	39.03	45.00
39	38.00	40.03	46.00
40	39.00	41.03	47.00

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C ~ 85°C。
3. 额定电压: 50V, AC/DC(等效)。
4. 接触电阻: ≤ 0.03Ω。
5. 绝缘电阻: ≥ 500MΩ。
6. 产品料号:

LW10252-XX X X

NO OF CRT (产品PIN数)

Plating(电镀方式)

0: 端子全镀锡

1: 端子全金 (G/F OVERALL)

2: 端子半金锡

Packing(包装方式)

T: TUBE管装

R: TAPE & REEL 卷装

X.	± 0.30	X.°	± 5°	UNITS	mm
.X	± 0.20	.X°	± 2°	MAT'L	
.XX	± 0.10	.XX°	± 1°		
.XXX ± 0.05	.XXX° ± 0.5°			FINISH	

NAME(INTENDED USE)		PART NO.(INTENDED USE)	
FPC CONNECTOR		APPD: SUNNY	
		CHKD: LISA	
		DR: ZOE	2015-1-28

TITLE:		DWG NO.:	
MINTRON CO., LTD.		LW10252-XXXX	
FPC1.0K型防式下接 (H=2.5)		SCALE	1/1
SHEET	1/1	REV.	A