




说明:

1. 材质:

胶芯:PBT,UL94V-0; COLOR; BLACK

端子: C5191

外壳: C2680

2. 电镀说明:

端子: 镍底, 镀金G.F

外壳: 表面镀镍

3. 性能说明:

1) 电压: 150VACRMS.

2) 额定电流: 1.5A.


3) 接触电阻: 40mΩ Max.

4) 绝缘电阻: 500MΩ MIN.

5) 绝缘耐压: 1000VAC.

6) 工作温度: -25° C TO +85° C.

7) 耐久性: 500 Mating Cycles MIN.



PC Board Layout
Component Side Shown

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: RJ45-10P/8C 59A-1*2 弯插 带屏蔽 带灯左黄右绿 无弹			
DRAWN: ZYJ	DATE: 2020-07-10	PART. NO.	R-RJ45R08P-C203		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0413	REV.	A HY04