








- 1.CIRCUIT: ON/OFF
- 2."  $\bigcirc$  "DENOTES CRITICAL DIMENSIONS.
- 3.Operation force : 800±300gf
- 4.RATING:16A GP 125/250VAC 3/4HP 125/250VAC T125(CUL)  
16(4)A 125/250V~ T125/55(ENEC17;NEMKO;CB)  
6(4)A 250~ T125/55(CQC)
- 5.Contact resistance : <30m $\Omega$
- 6.Insulation resistance : >100M $\Omega$ (500VDC between open contacts)
- 7.Dielectric strength : >1500Vac 0.5mA 1 minute  $\triangle$ 3
- 8.ACTUATOR COLOR:WHITE  
HOUSING COLOR:WHITE  
BASE COLOR:BLACK
- 9.ALL MATERIALS ARE ROHS COMPLIANT



A	$\triangle$ 5	→	$\triangle$ 10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		A		
	$\triangle$ 4	→	$\triangle$ 9	→	RANGE	TOLERANCE				LMC	SCALE	NO				
	$\triangle$ 3	→	$\triangle$ 8	→	X	±0.30				2020.11.14	MAT'L	***				
	$\triangle$ 2	增加性能标准	$\triangle$ 7	→	X.X	±0.20					MATERIAL NO.				DRAWING NO.	REV.
	$\triangle$ 1	安规刻字修改	$\triangle$ 6	→	X.XX	±0.10					MPS21-WWBCB-S1-A				WIF118001	B0
	NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.									

4

3

2

1