








REV.	ECN. NO.	APPD.
A		
序号	品名	材质
①	0.5拉拔三代板芯 (012.0)	ICP U6940 本色
②	0.5拉拔三代下接脚子 (012.0)	磷青铜/表面镀锡 镀金
③	0.5拉拔第三代百基 (012.0)	ICP U6940 黑色
④	0.5拉拔三代铜片 (012.0)	黄铜/表面镀锡



SECTION A-A



CKT	DIM A	DIM B	DIM C	DIM D	CKT	DIM A	DIM B	DIM C	DIM D
4	1.50	2.56	7.60		33	16.00	17.06	22.10	
5	2.00	3.06	8.10		34	16.50	17.56	22.60	5.20
6	2.50	3.56	8.60		35	17.00	18.06	23.10	
7	3.00	4.06	9.10		36	17.50	18.56	23.60	
8	3.50	4.56	9.60		37	18.00	19.06	24.10	
9	4.00	5.06	10.10		38	18.50	19.56	24.60	
10	4.50	5.56	10.60		39	19.00	20.06	25.10	
11	5.00	6.06	11.10		40	19.50	20.56	25.60	
12	5.50	6.56	11.60		41	20.00	21.06	26.10	
13	6.00	7.06	12.10		42	20.50	21.56	26.60	
14	6.50	7.56	12.60		43	21.00	22.06	27.10	
15	7.00	8.06	13.10		44	21.50	22.56	27.60	
16	7.50	8.56	13.60		45	22.00	23.06	28.10	
17	8.00	9.06	14.10		46	22.50	23.56	28.60	
18	8.50	9.56	14.60	5.20	47	23.00	24.06	29.10	
19	9.00	10.06	15.10		48	23.50	24.56	29.60	5.75
20	9.50	10.56	15.60		49	24.00	25.06	30.10	
21	10.00	11.06	16.10		50	24.50	25.56	30.60	
22	10.50	11.56	16.60		51	25.00	26.06	31.10	
23	11.00	12.06	17.10		52	25.50	26.56	31.60	
24	11.50	12.56	17.60		53	26.00	27.06	32.10	
25	12.00	13.06	18.10		54	26.50	27.56	32.60	
26	12.50	13.56	18.60		55	27.00	28.06	33.10	
27	13.00	14.06	19.10		56	27.50	28.56	33.60	
28	13.50	14.56	19.60		57	28.00	29.06	34.10	
29	14.00	15.06	20.10		58	28.50	29.56	34.60	
30	14.50	15.56	20.60		59	29.00	30.06	35.10	
31	15.00	16.06	21.10		60	29.50	30.56	35.60	
32	15.50	16.56	21.60						

技术指标:

1. 塑件表面应光洁, 无毛边, 无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC/DC(等效).
4. 接触电阻: $\leq 0.03\Omega$.
5. 绝缘电阻: $\geq 500M\Omega$.
6. 产品料号:

LW05202—XX X X


NO OF CKT(产品PIN数)

Plating(电镀方式)

0: 端子全穿锡
1: 端子全金(C/F OVERALL)
2: 端子半金锡

Packing(包装方式)

T: TUBE管装
R: TAPE & REEL卷装



适用扁平线

X.	± 0.30	X°	$\pm 5^{\circ}$	UNITS	mm
.X	± 0.20	.X°	$\pm 2^{\circ}$	MATL	
.XX	± 0.10	.XX°	$\pm 1^{\circ}$		
.XXX	± 0.05	.XXX°	$\pm 0.5^{\circ}$	FINISH	

NAME(INTENDED USE)		PART NO.(INTENDED USE)	
APPD:	SUNNY	DR:	ZOE
CHKD:	USA		2015-1-28

TITLE:		DWG NO.:	
FPC0.5 拉拔脚式全包下接 (H=2.0)		LW05202-XXXX	
SCALE	1/1	SHEET	1/1
REV.	A		

MINTRON CO., LTD.

