



REV.	ECN. NO.	APPD.
A		

NOTES:
 Current Rating:3.0AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:-40℃ to +105℃

Contact Material:Brass
 Contact plating:Au or Sn Over Ni
 Insulator Material:PBT or PA6T+30%GF(UL94V-0)





Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)




Ordering Information

MTP125-12XXR2

No.of Pins per
 Row: 01~40



Dimension antitheses list			
ITEM	A	B	D
Standard	3.00	6.00	1.20
Alternate			

X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)		MINTRON CO.,LTD.			
.X ± 0.20	.X° ± 2°	MAT'L	PART NO.(INTENDED USE)		TITLE: MTP125-12XXR2			
.XX ± 0.10	.XX° ± 1°							
.XXX ± 0.05	.XXX° ± 0.5°	FINISH	APPD: SUNNY		DWG NO.:			
PIN HEADER CONNECTOR		Q'TY	CHKD: LISA					
			DR: ZOE 2006-11-28			SCALE 1/1	SHEET 1/1	REV. A