


३



Rating: 16A 125V AC (UL CUL)

16A 250V AC (UL CUL TUV ENEC CB CQC)

Contact Resistance: 50m Ω (Max)

Insulation Resistance: DC 500V 100M Ω (Min)

Dielectric Strength: AC1500V 1 minute




Electrical life: 10,000 cycles

Operating Temperature: 0°C~85°C

Safety Approval:    



CUT-OUT



ON-OFF

MATERIAL:

Body:Nylon66,UL rated:94V-2 min

Actuator: PC/Nylon66, UL rated: 94V-2 min

Terminal: Brass with silver-plate

Marking	
X	
0	None
1	
2	
3	
4	
5	
7	
8	
9	
B	
C	
E	
F	
G	

			公差 TOLERANCES		.X $\pm$ 0.3 .XX $\pm$ 0.15		角度 $\pm$ 1°		单位 DIMENSION UNIT		mm.
			版本 VERSION	A0	比例尺 SCALE	NONE	日期 DATE	2020.08.25	品名 TITLE	图号 DRAWING NO	
			核准		核对 CHECKED BY	Z. H. B.	绘图 DRAWN BY	王立权	R-210-C5L-BG-A1		
版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	APPROVED BY							