FEATURES

- Material: Warp proof self-extinguishing UL approved PVC, 94V-0 flammability rating, M1 rating NF fire resistant test.

- Color: White

- These devices are for routing of wires within devices in factory installations.

- Features parallel holes on both sidewalls to facilitate cutting in wire application.

- Special color, size, length upon request of reasonable quantity.

RS PRO Wiring Duct

RS Stock No.: 2339184

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

- Material: Warp proof self-extinguishing UL approved PVC, 94V-0 flammability rating, M1 rating NF fire resistant test.
- Color: White
- Vicat softening point: 86℃
- UL Test up to 50℃
- These devices are for routing of wires within devices in factory installations.
- SOLID: No slot design, for external wiring or where wire extraction is not necessary.
- Solid type can protect wire from external damage such dust or mouse.
- Special color, size, length upon request of reasonable quantity.
  - Regular wiring duct cover can be upgrade to NON-SLIP ones which improves tightness between duct and cover, benefits vertical installations, and improves effectiveness and avoid cover slip off.

General Specifications

Series	Wiring Duct
Type	
Colour	White
Material	PVC
UV Resistant	NO
Minimum Operating Temperature	0℃
Maximum Operating Temperature	Vicat softening point: 86℃, UL Test up to 50℃
Fire Behaviour	Self-Extinguishing
Quantity	2M

Mechanical Specifications

Unit:mm

W x H (mm)	Wires to be Contained (16-14 AWG)	Length	Color
15x25	5~12pcs	2M	White

Approvals

Declarations	
Standards Met	UL, CSA, RoHS

Similar Products

Stock No.	Brand	Product Name	Colour	Material