











REVISIONS				
P	LTN	DESCRIPTION	DATE	OWN APVD
A1		INCREASE PN	14SEP2022	X.F E. J
A2		INCREASE PN	14SEP2022	X.F E. J
A3		ECN-24-263260	19APR2024	W.Z E. J
A5		ECN-25-312859	24MAR2025	F.H E. J



- △ MATERIAL :
TYPE : PA66 GF30 V0 FLAME RETARDANT MATERIAL
COLOR : SEE TABLE
- 2. FEATURES DENOTED BY REFERENCE DIMENSIONS
MUST BE INSPECTED FOR PRESENCE
- 3. PART MUST BE FREE OF EXCESSIVE FLASH, MIS-MATCH,
SINK MARKS, OR OTHER VISUAL IMPERFECTIONS THAT
MAY AFFECT PRODUCT FIT FORM OR FUNCTION
- △ 4 CIRCUIT ID
- 5. FOR HB VERSION REFER TO DRAWING 2103181



-1 AS SHOWN

A5	COLOR	MIN WIRE	MAX O.D.	F	DESCRIPTION	TE P/N
BLACK	4.00	4.40	4.50	CABLE SEAL RETAINER, SIZE E	1-2310469-6	
BLACK	5.48	6.10	6.20	CABLE SEAL RETAINER, SIZE C	1-2310469-5	
BLACK	4.76	5.48	5.60	CABLE SEAL RETAINER, SIZE B	1-2310469-4	
BLACK	4.20	4.70	4.80	CABLE SEAL RETAINER, SIZE A	1-2310469-3	
RED	4.50	5.10	5.10	CABLE SEAL RETAINER, SIZE D	2310469-3	
DK GRAY	5.48	6.10	6.20	CABLE SEAL RETAINER, SIZE C	2310469-2	
ORANGE	4.76	5.48	5.60	CABLE SEAL RETAINER, SIZE B	2310469-1	

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009. TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±0.2
1 PLC	±0.3
2 PLC	±0.4
3 PLC	±0.100
4 PLC	±0.0001
ANGLES	±1°
FINISH	-

APVD: J. YIN 26JUN2017
 NAME: CABLE SEAL RETAINER HVA280-2PHI XE
 PRODUCT SPEC: 108-2394
 APPLICATION SPEC: 114-13295
 WEIGHT: -
 CUSTOMER DRAWING: -
 SCALE: 4:1
 SHEET: 1 OF 1
 REV: A5