

Features

- Cable lockout
- 6 holes
- Suitable for 8mm padlock shackles
- Injection moulded body with Steel hasp
- Withstand temperature of -20 to +65°C
- Supplied with 2m Vinyl coated Steel cable
- Highly visible red colour
- Weight of 300g

RS PRO Multi Lockout + 2m vinyl coated steel cable with loop

RS Stock No.: 1615874



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.*
- *Multipurpose Cable Lockout is being used on various applications including on the Gate valves, electrical panels, Electrical Switches, etc.*
- *Accepts padlocks with a shackle diameter up to 8 mm.*
- *Up to 6 lockout Padlocks can be installed on each device.*
- *Injection moulded one set construction outer body incorporating corrosion free steel inner hasp – having long lasting life.*
- *Withstand temperature (+65 degree C to – 20 degree C).*
- *Cost effective, easy to use device that is as efficient as steel chain but are much lighter and more visible.*
- *Interlocked / looped corner 2 meter cable is provided with each lockout device.*
-

General Specifications

Cable size	2 meter with loop
Weight	around 300 grams per set
Package includes	Packed single unit in PVC clear polythene bag.
Type	Cable Lock
Colour	Red
Number of Locks	6
Material	PP
For Use With	Gate Valves, Electrical Panels, Electrical Switches

ories